


Class I Polypropylene Disposable Laboratory Coats

These unisex polypropylene laboratory coats with back slit have five stud fasteners and elasticated cuffs, without pockets. They provide safety and comfort in the lab environment for non-critical applications.

- White spunbond polypropylene
- Elasticated cuffs
- Fabric weight: 40g/m²
- Standard single collar, no pockets
- Complies with 93/42/EEC
- Back slits
- Five snap fasteners for a secure closure
- Unisex
- AQL 0.65 for visual defects
- Carton of 100 coats individually bagged
- Low linting - Suitable for use in ISO Class 5/6 clean-room environments



Lab Coat only



Cat. No	16844733	16692103	16682103	16602113	16612113	
Size	S	M	L	XL	2XL	+ -ERROR
A Length, cm	92	100	102	104	109	±2
B Chest width, cm	63	69	71	73	75	±1
C Sleeve and Shoulder length, cm	73	77	78	79	80	±1
D Shoulder width, cm	15	16	16	17	18	±0.5
E Back slit length, cm	27	27	27	27	27	±1

Austria: fishersci.at Belgium: fishersci.be Denmark: fishersci.dk
 Germany: fishersci.de Ireland: fishersci.ie Italy: fishersci.it
 Finland: fishersci.fi France: fishersci.fr Netherlands: fishersci.nl
 Norway: fishersci.no Portugal: fishersci.pt Spain: fishersci.es
 Sweden: fishersci.se Switzerland: fishersci.ch UK: fishersci.co.uk

