

Microflex

Microflex XCEED® Powder-Free Nitrile Gloves

Unparalleled Comfort

Industry Leading Protection, Strength and Value

STRENGTH

Microflex Avantex® technology allows the production of lighter, thinner nitrile disposable gloves with a supple softness and relaxed comfort that rivals the fit of latex while delivering 60% increased strength and durability to protect hard working hands.

COMFORT

Prolonged muscle effort over longer periods of time can cause hand fatigue, which has been associated with Carpel Tunnel Syndrome, as well as other hand injuries. In a comprehensive study by the industry leader in ergonomic testing and certifications in the U.S., XCEED® gloves markedly reduced muscle effort when performing test manipulations as compared to a leading competitor's glove.

ADVANCED BARRIER PROTECTION

The combination of Avantex® polymer technology and state-of-the-art manufacturing techniques delivers exceptionally consistent gloves with the lowest pinhole rates in the industry. XCEED® gloves have a freedom from holes of AQL 0.65.

VALUE

XCEED® gloves are packed 250 gloves per box, providing you as much value in a single dispenser box as possible and reducing waste.



Cat. No	Alt No	Size	Quantity
15289373	XC-INT-XS	Extra Small	Box of 250 Gloves
15269373	XC-INT-S	Small	Box of 250 Gloves
15259373	XC-INT-M	Medium	Box of 250 Gloves
15249373	XC-INT-L	Large	Box of 250 Gloves
15279373	XC-INT-XL	Extra Large	Box of 250 Gloves

Ordering Details

Microflex XCEED®, Category III, EN374-2; AQL .65, ISO 13485

Microflex Supreno® SE Powder-Free Nitrile Gloves



Supreno gloves provide the durability needed for high-risk applications. Offering all the benefits of a nitrile glove, Supreno® meets your demand for strength and comfort.

Ordering Details

Microflex Supreno® SE Category III, EN374-2;
AQL .65, ISO 13485

Cat. No	Alt No	Size	Quantity
15299363	SU-INT-XS	Extra Small	Box of 100 Gloves
15279363	SU-INT-S	Small	Box of 100 Gloves
15269363	SU-INT-M	Medium	Box of 100 Gloves
15259363	SU-INT-L	Large	Box of 100 Gloves
15289363	SU-INT-XL	Extra Large	Box of 100 Gloves

Microflex Diamond Grip Plus™ Latex Gloves



Polymer-coated for easy donning. Longer and thicker than typical disposable gloves for added protection. Textured for a secure grip in wet or dry conditions. Premium, low-modulus natural rubber latex for a true fit and reduced hand fatigue.

Ordering Details

Microflex Diamond Grip Plus®, Category III,
EN374-2; AQL 1.5, ISO 13485

Cat. No	Alt No	Size	Quantity
15299353	DGP-INT-XS	Extra Small	Box of 100 Gloves
15279353	DGP-INT-S	Small	Box of 100 Gloves
15269353	DGP-INT-M	Medium	Box of 100 Gloves
15269333	DGP-INT-L	Large	Box of 100 Gloves
15289353	DGP-INT-XL	Extra Large	Box of 100 Gloves

Gloves specifications

	Supreno®	XCEED® International	Diamond Grip Plus™ International
Length (mm)	245	240	245
Cuff Thickness (mm) (ISO 11193)	0.09	0.06	0.1
Palm Thickness (mm) (ISO 11193)	0.11	0.07	0.13
Finger Thickness (mm) (ISO 11193)	0.18	0.11	0.16
Tensile Strength (MPa)	36	33	22
Force at Break (Newtons)	10	7	9
Elongation (%) (ISO 11193)	500	500	700
Protein Level	n/a	n/a	max. 50 µg/g

MICROFLEX®
THE MOST TRUSTED NAME IN GLOVES®

© 2014 Thermo Fisher Scientific Inc. All rights reserved.
Trademarks used are owned as indicated at www.fishersci.com/trademarks.

Austria: +43(0)800-20 88 40 Belgium: +32 (0)56 260 260 Denmark: +45 70 27 99 20
Germany: +49 2304 932-5 Ireland: +353 (0)1 885 5854 Italy: +39 02 950 59 478
Finland: +358 (0)9 8027 6280 France: +33 (0)3 88 67 14 14 Netherlands: +31 (0)20 487 70 00
Norway: +47 22 95 59 59 Portugal: +351 21 425 33 50 Spain: +34 902 239 303
Sweden: +41 31 352 32 00 Switzerland: +41 (0)56 618 41 11 UK: +44 (0)1509 555 500

**Fisher
Scientific**

A Thermo Fisher Scientific Brand