

Corning® Gosselin™ Containers

CORNING

Choose from a range of containers dedicated to sample collection and sample storage across different applications.

Depending on your needs, the different cap types, product shapes, and colors will allow you to efficiently collect, store, and identify your samples.

All containers are produced with high-tech equipments using molding technology. Most of our products are assembled in line to avoid any external contaminations. The raw plastics used are virgin and comply with the environmental standards in force.

*Corning suppliers guarantee the quality of their raw materials through a certificate of compliance. However, the finished products have not been validated for food contact applications. They are designed for laboratory applications only.

Key Features

- ▶ Cap type and product shape to fit sample collection needs
- ▶ Colored caps to easily identify the samples
- ▶ Packaging perfectly adapted to the user's needs: single bag, packing of containers into boxes, screw-capped containers wrapped on trays.
- ▶ Raw materials of containers are food contact grade (comply with 1935/2004/EC and 10/2011/EC)*



Ordering Information

Corning® Gosselin™ Containers

Straight containers, polypropylene, screw cap



Cat. No.	Volume (mL)	Height (mm)	Diam. (mm)	Cap Type	Sterile	Qty/Pk	Qty/Cs
TP30C-002*	40	70	30		Yes	100	1000
TP30C-003*	40	70	30		Yes	100	1000
TP30C-013*	40	70	30		No	100	1000
TP35C-002	60	70	33		Yes	70	700
TP35C-001*	60	70	33		Yes	70	700
TP35C-013	60	70	33		No	70	700
TP52C-002	125	74	52		Yes	380	380
TP52C-003*	125	74	52		Yes	380	380
TP52C-001*	125	74	52		Yes	380	380
TP53C-002	180	102	52		Yes	264	264
TP53C-003*	180	102	52		Yes	264	264
TP53C-001*	180	102	52		Yes	264	264

*Not available in North America.

Conical Containers, polypropylene, snap cap



Cat. No.	Volume (mL)	Height (mm)	Diam. (mm)	Cap Type	Sterile	Qty/Cs
PC200A-02	200	88	62		Yes	220
PC200A-07	200	88	62		Yes	220
PC400-03	400	100	85		Yes	185
PC400-05	400	100	85		Yes	185
PC1000-05	1000	130	105		Yes	80
PC1000-04	1000	130	105		Yes	80

Straight containers, hinged cap, polypropylene



Cat. No.	Volume (mL)	Height (mm)	Diam. (mm)	Cap Type	Writing Area	Sterile	Qty/Cs
FL52-02	45	85	29		Yes	Yes	650
FL60-04	50	78	31		Yes	Yes	650
FL60-05*	50	78	31		Yes	No	650
FL100-05	90	80	43		Yes	Yes	350
FL100-04*	90	80	43		Yes	No	350
FL300-04	300	88	75		No	Yes	240
FL300-02*	300	88	75		No	No	240

*Not available in North America.

Corning® Gosselin™ Containers (continued)

Dippers, polypropylene, with removable handle



Cat. No.	Cap	Volume (mL)	Height (mm)	Height with handle (mm)	Diam. (mm)	Sterile	Qty/Pk	Qty/Cs
TAT30C-01	Screw	40	70	275	30	Yes	1	250
TAF11-01	Hinged	90	80	290	43	Yes	1	150
TAT52C-01	Screw	125	74	275	52	Yes	1	100
TAT53C-02	Screw	180	102	305	52	Yes	1	100

Warranty/Disclaimer: Unless otherwise specified, all products are for research use or general laboratory use only.* Not intended for use in diagnostic or therapeutic procedures. Not for use in humans. These products are not intended to mitigate the presence of microorganisms on surfaces or in the environment, where such organisms can be deleterious to humans or the environment. Corning Life Sciences makes no claims regarding the performance of these products for clinical or diagnostic applications. *For a listing of US medical devices, regulatory classifications or specific information on claims, visit www.corning.com/resources.

Corning's products are not specifically designed and tested for diagnostic testing. Many Corning products, though not specific for diagnostic testing, can be used in the workflow and preparation of the test at the customers discretion. Customers may use these products to support their claims. We cannot make any claims or statements that our products are approved for diagnostic testing either directly or indirectly. The customer is responsible for any testing, validation, and/or regulatory submissions that may be required to support the safety and efficacy of their intended application.

CORNING

Corning Incorporated
Life Sciences

www.corning.com/lifesciences

NORTH AMERICA

t 800.492.1110

t 978.442.2200

ASIA/PACIFIC

Australia/New Zealand

t 61 427286832

Chinese Mainland

t 86 21 3338 4338

India

t 91 124 4604000

Japan

t 81 3-3586 1996

Korea

t 82 2-796-9500

Singapore

t 65 6572-9740

Taiwan

t 886 2-2716-0338

EUROPE

CSEurope@corning.com

France

t 0800 916 882

Germany

t 0800 101 1153

The Netherlands

t 020 655 79 28

United Kingdom

t 0800 376 8660

All Other European Countries

t +31 (0) 206 59 60 51

LATIN AMERICA

grupolA@corning.com

Brazil

t 55 (11) 3089-7400

Mexico

t (52-81) 8158-8400