

## Guaranteed leakproof system

Keep your precious solutions  
safe and secure

### Thermo Scientific™ Nalgene™ PET & PETG media bottles

- Bottles are compatible with Nalgene Standard, Septum, and Tamper Evident Closures and provide a leakproof\* seal
- High quality virgin resins are non-cytotoxic, non-pyrogenic, non-mutagenic, and are made with Animal Derived Component Free† materials to help ensure content purity
- Keeps your products safe by meeting the latest biological testing standards including USP Class VI, USP 37 <661>, and ISO 10993-3
- Unparalleled Product Validation Support helps save you time and money

We manufacture both the bottle and closure to ensure high performance of the total package.

Our bottles are made from durable, break-resistant polyethylene terephthalate (PET) or glycol modified (PETG) resins with natural high density polyethylene closures.

The unique Thermo Scientific™ Nalgene™ closure and bottle design requires no liner or gasket to provide repeatable leakproof\* performance, and in general, provides an effective oxygen and carbon dioxide barrier to maintain the appropriate pH of your reagents.

A 10<sup>-6</sup> SAL provides greater sterility assurance for your contained reagents.



**GUARANTEED LEAKPROOF**

### Square PET Media Bottles, Shrink-Wrapped Trays

| Cat. No.    | Color       | Sterility | Capacity | Closure Type          | Closure Size | Quantity per tray/case |
|-------------|-------------|-----------|----------|-----------------------|--------------|------------------------|
| 842040-0125 | Transparent | Sterile   | 125mL    | Natural HDPE Closures | 38-430       | 24/96                  |
| 342040-0250 | Transparent | Sterile   | 250mL    |                       | 38-430       | 30/60                  |
| 842040-0650 | Transparent | Sterile   | 650mL    |                       | 38-430       | 24/48                  |
| 842040-1000 | Transparent | Sterile   | 1000mL   |                       | 38-430       | 12/24                  |
| 842044-0125 | Transparent | Sterile   | 125mL    | No Closures           | 38-430       | 24/96                  |
| 342044-0650 | Transparent | Sterile   | 650mL    |                       | 38-430       | 24/48                  |
| 342044-1000 | Transparent | Sterile   | 1000mL   |                       | 38-430       | 12/24                  |

### Square PETG Media Bottles, Shrink-Wrapped Trays

| Cat. No.    | Color       | Sterility   | Capacity | Closure Type                                    | Closure Size | Quantity per tray/case |
|-------------|-------------|-------------|----------|---|--------------|------------------------|
| 322020-0030 | Transparent | Non-sterile | 30mL     | Natural HDPE Closures                           | 20-415       | 40/280                 |
| 322020-0060 | Transparent | Non-sterile | 60mL     |   | 24-415       | 40/200                 |
| 322020-0125 | Transparent | Non-sterile | 125mL    |   | 38-430       | 24/96                  |
| 322020-0250 | Transparent | Non-sterile | 250mL    |   | 38-430       | 30/60                  |
| 322020-0500 | Transparent | Non-sterile | 500mL    |   | 38-430       | 20/40                  |
| 322020-1000 | Transparent | Non-sterile | 1000mL   |   | 38-430       | 12/24                  |
| 322020-2000 | Transparent | Non-sterile | 2000mL   |   | 53B          | 6/12                   |
| 342020-0030 | Transparent | Sterile     | 30mL     | Natural HDPE Closures                           | 20-415       | 40/280                 |
| 342020-0060 | Transparent | Sterile     | 60mL     |   | 24-415       | 40/200                 |
| 342020-0125 | Transparent | Sterile     | 125mL    |   | 38-430       | 24/96                  |
| 342020-0250 | Transparent | Sterile     | 250mL    |   | 38-430       | 30/60                  |
| 342020-0500 | Transparent | Sterile     | 500mL    |   | 38-430       | 20/40                  |
| 342020-1000 | Transparent | Sterile     | 1000mL   |   | 38-430       | 12/24                  |
| 342020-2000 | Transparent | Sterile     | 2000mL   |   | 53B          | 6/12                   |
| 342020-9500 | Transparent | Sterile     | 650mL    | 38-430  | 24/48        |                        |
| 322021-0030 | Amber       | Non-sterile | 30mL     | Amber HDPE Closures                             | 20-415       | 40/280                 |
| 322021-0060 | Amber       | Non-sterile | 60mL     |   | 24-415       | 40/200                 |
| 322021-0125 | Amber       | Non-sterile | 125mL    |   | 38-430       | 24/96                  |
| 342023-0060 | Transparent | Sterile     | 60mL     | Natural HDPE Closures with silicone/PTFE septum | 24-415       | 40/200                 |
| 342023-0125 | Transparent | Sterile     | 125mL    |   | 38-430       | 24/96                  |
| 342023-0500 | Transparent | Sterile     | 500mL    |   | 38-430       | 20/40                  |
| 342023-1000 | Transparent | Sterile     | 1000mL   |   | 38-430       | 12/24                  |
| 342023-9500 | Transparent | Sterile     | 650mL    |   | 38-430       | 24/48                  |
| 342024-0030 | Transparent | Sterile     | 30mL     | No Closures                                     | 20-415       | 40/280                 |
| 342024-0060 | Transparent | Sterile     | 60mL     |   | 24-415       | 40/200                 |
| 342024-0125 | Transparent | Sterile     | 125mL    |   | 38-430       | 24/96                  |
| 342024-0250 | Transparent | Sterile     | 250mL    |   | 38-430       | 30/60                  |
| 342024-0500 | Transparent | Sterile     | 500mL    |   | 38-430       | 20/40                  |
| 342024-1000 | Transparent | Sterile     | 1000mL   |   | 38-430       | 12/24                  |

### Bulk Packed Closures

| Cat. No.    | Sterility | Closure Type                                    | Closure Size        | Quantity per case |
|-------------|-----------|---|---------------------|-------------------|
| 342151-0200 | Sterile   | Natural HDPE Closures                           | 20-415              | 280               |
| 342151-0240 | Sterile   |   | 24-415              | 240               |
| 342151-0384 | Sterile   |   | 38-430              | 200               |
| 342141-0384 | Sterile   | Natural HDPE Tamper Evident Closures            | 38-430 <sup>†</sup> | 240               |
| 342178-0240 | Sterile   | Natural HDPE Closures with silicone/PTFE septum | 24-415              | 200               |
| 342178-0384 | Sterile   |   | 38-430              | 240               |

<sup>†</sup> Not compatible with 125mL PETG Bottles

#### Change notification database



Compliance with ISO 13485-2003 or ISO 9001-2008 and cGMP requirements mean that changes to manufacturing procedures, packaging and product specifications are all documented and traceable. To be sure you receive change notifications, please register at [www.thermoscientific.com/notifications](http://www.thermoscientific.com/notifications)

#### Certificates



Many of our resin manufacturers submit DMF's to the FDA as noted in our product certificates. Certificates of Compliance (COCs) are available at [www.nniassetbank.com](http://www.nniassetbank.com) or on [www.thermofisher.com](http://www.thermofisher.com).

#### Documentation Support



Detailed Validation Binders and Forced Extraction Studies provide baseline data designed to reduce the likelihood of immediate compatibility concerns with the contained materials. This confidential information can be requested at: [rocrgsupport@thermofisher.com](mailto:rocrgsupport@thermofisher.com) Following your request submission, a Confidentiality Agreement will be forwarded to you for completion.

*\*Our guarantee for a leakproof seal is subject to our standard product warranty, as set forth in the Thermo Fisher Scientific Terms and Conditions of Sale. Our products are leakproof at ambient temperature and pressure when used with their corresponding closures. However customers are advised to test our containers and closures under conditions of their planned applications. Please contact [technicalsupport@thermofisher.com](mailto:technicalsupport@thermofisher.com) if you need additional information about our products.*

*†Except products made with the amber colorant.*

Find out more at: [www.thermofisher.com/mediabottles](http://www.thermofisher.com/mediabottles)  
[diagnosticsandpackaging.thermoscientific.com](http://diagnosticsandpackaging.thermoscientific.com)