KIMTECH

Kimtech[™] Polaris[™] Nitrile Gloves

- Textured fingertips
- Enhanced chemical and biohazard protection
- Optimal skin health protection

BUILT FOR SCIENCE - MADE FOR YOU

Kimtech™ Polaris™ Nitrile Gloves have been designed for use in laboratories, life science applications and non-sterile pharmaceutical manufacturing environments.

With proven protection against the harshest chemicals, superior dexterity and comfort you can count on, these gloves are built for science, made for you.







•+29 common chemicals tested •+24 Cytotoxic

drugs tested

Recyclable with our RightCycle™ Programme



Size Guide	XS (5.5)	S (6.5)	M (7.5)	L (8.5)	XL (9.0)		
Codes	62000	62001	62002	62003	62004		
Dookoging	Sizes XS to L: 100 gloves per dispenser - 10 dispensers per case (= 1000 gloves)						
Packaging	Size XL: 90 gloves per dispenser - 10 dispensers per case (= 900 gloves)						



Description

Formulation	High grade synthetic nitrile rubber (acrylonitrile - butadiene)
Technology	Optimized nitrile formulation for extended chemical splash protection with no compromise on wearer comfort
Design	Dark Magenta, Ambidextrous, beaded cuff, textured fingertips

Assured Compliance

CE/UKCA	PPE Cat III according to Regulation (EU) 2016/425 and to the Regulation 2016/425 as brought into UK law and amended.				
EU PPE norms	EN ISO 374-1 Type B (JKOPT) Chemical Splash Protection EN 374-4 Resistance to Degradation by Chemicals EN 374-5 Micro-Organism and Virus Protection				
Other Standards	ASTM D6978 Chemotherapy Drug Splash Protection ISO 10993 Bio-compatibility Food contact approved. Compliant with German BfR Recommendation XXI and XXI/1 and Regulation (EU) 2019/515				
Quality Assurance	Quality System of the Manufacturing Facility compliant with ISO 9001, ISO 13485 and 21 CFR Part 820				

Residual Content

Vulcanization Agent	Non detectable level of vulcanization agent in the finished product			
Powder	Powder-free glove with a maximal residual powder content <2.0 mg/glove			
Latex Protein	Not made with natural rubber latex			

Documentation

Certifcate of Analysis (CoA)	Certificate of Analysis available for each production lot at www.certs.kcprofessional.com
Declaration of Conformity (DoC)	Declaration of Conformity available from the product page on www.kimtech.eu
User Instructions	Printed on the dispenser box

Product Specifications

Characteristics	Value AQL 0.65(as defined per ISO 2859-1 sampling by attributes)				Test method			
Freedom from holes					EN 374-2			
Tensile properties	Tensile	nin.)	Elongation at Break (min.)					
Before Aging After Aging	≥ 14 MPa ≥ 14 MPa				≥ 500%, min. ≥ 400%, min.		ASTM D412 ASTM D573 ASTM D6319	
Dimension		Target Thickness/Width/ Length						
Thickness (mm)	Middle Finger 0.15		Palm 0.12			Cuff 0.09	ASTM D6319 EN 455-2	
Palm width (mm)	XS	S	М		L	XL	ASTM D6319	
Faim widin (min)	70	80	95		110	120	EN 455-2	
Length (mm)	Length (mm) 250				EN ISO 21420			

Find it at eu.fishersci.com

Distributed by Fisher Scientific. Contact us today:

Austria: fishersci.at Belgium: fishersci.be Denmark: fishersci.dk Germany: fishersci.de Ireland: fishersci.ie Italy: fishersci.it Finland: fishersci.fi France: fishersci.fr Netherlands: fishersci.nl Norway: fishersci.no Portugal: fishersci.pt Spain: fishersci.es Sweden: fishersci.se Switzerland: fishersci.ch UK: fishersci.co.uk

